

Transcend AUTO™



The Transcend Auto™ is the world's smallest, lightest, most innovative fully-featured APAP. Weighing less than 430 grams, Transcend Auto is the perfect primary-use APAP that travels well. Small in size and big on features, Transcend Auto includes new Transcend EZEX™ Technology, which provides pressure relief on exhalation. It also offers unique accessories to fit the patient's lifestyle, such as small batteries for uninterrupted therapy, a solar battery charger, hassle-free Waterless Humidification™ Systems and Bluetooth® wireless compliance reporting*. Transcend innovation is changing the way sleep apnea therapy is delivered.

- Small, fully-featured APAP
- Transcend EZEX pressure relief technology
- Weighs less than 430 g
- Ramp feature
- Automatic altitude adjustment
- AHI & leak detect
- Up to 13 months compliance data storage
- Compatible with P4 and P8 Batteries™ and Portable Solar Charger
- Compatible with Transcend Waterless Humidification System and Transcend Heated Humidifier™

*Available with purchase of the Transync™ Bluetooth dongle.

E: sales@brmed.net

W: www.brmed.net

AUSTRALIA 1800 335 333

P.O. Box 4, West Ryde, NSW 1685

NEW ZEALAND 0800 335 333

P.O. Box 76640 Auckland 2241

	Transcend AUTO	Transcend EZEX	Transcend
Therapy Mode			
Auto-titrating	X		
Fixed-pressure	X	X	X
Hardware Features			
Dimensions (LxWxH)	15.5 cm x 8.9 cm x 7.1 cm		
Weight	426 g		
Sound pressure levels	26.6 dB	26.6 dB	29 dB
Operating Pressure (4-20 cmH2O)	X	X	X
EZEX pressure relief (settings 1,2,3)	X	X	
Ramp (0-45 min), adjustable	X	X	X
Automatic altitude adjustment ≤ 2,438m	X	X	X
Power supply: 100 - 240 VAC, 50-60Hz, 19VDC, 2.6 Amp	X	X	X
Air filter: Disposable filter media	X	X	X
Operating range: 5° - 35° C, 10% - 80% relative humidity, non-condensing	X	X	X
Storage/transport range: -20° - 60° C, 10% - 90% relative humidity, non-condensing	X	X	X
Warranty: 2 years	X	X	X
EN60601-1: Class II Type BF, IP21 IEC 60601-1-2 EMC compatibility	X	X	IPX0
Compliance Data			
AHI & leak detect	X	X	X
Total therapy hours	X	X	X
Therapy sessions: adjustable settings, default ≥ 8 hours, 6 hours, and 4 hours	X	X	X
Total blower hours	X	X	X
13 months daily compliance storage	X	X	X
Adjustable date range selection	X	X	X
Summary data (unlimited, adjustable range)	X	X	X
Detailed data (unlimited, adjustable range)	X	X	X
Median snore index	X	X	
Median flow-limited breathing (%)	X	X	
Data Options			
Transfer via USB with Transcend Software	X	X	X
Email-capable data	X	X	X
TranSync wireless compliance	X	X	
Humidification			
Transcend Heated Humidifier™	X	X	X
Transcend Waterless Humidification™ System (HME)	X	X	X

Programming software and compliance reports available in multiple languages.
 Software compatible with Windows® 7, Windows® 8 and Windows® XP.
 Software upgrades available at www.MyTranscend.com/resources



E: sales@brmed.net

W: www.brmed.net

AUSTRALIA 1800 335 333

P.O. Box 4, West Ryde, NSW 1685

NEW ZEALAND 0800 335 333

P.O. Box 76640 Auckland 2241